

Produkt-Nr. Product No.	Anwendungen / Applications	Brennbereich / Firing range	Brennfarbe / Firing colour	Schamottierung / Chamotte		TS / DS %	Brennwindung / Firing shrinkage (%)			Wasseraufnahme / Water absorption (%)			WAK x 10 ⁻⁷ °C ⁻¹ (20-500 °C) / CTE x 10 ⁻⁷ °C ⁻¹ (20-500 °C)			Produkt-Nr. / Product No.
				Körnung / grain size (mm)	Anteil / Portion (%)		1070 °C	1140 °C	1200 °C 1240 °C	1070 °C	1140 °C	1200 °C 1240 °C	1070 °C	1140 °C	1200 °C 1240 °C	
DREHMASSEN / BODIES FOR THROWING																
24	Drehen / Throwing	1000 -1150 °C	weiß-hell / white-light	-	0	7	4	6	-	6	1	-	78	-	-	24
33	Drehen / Throwing	1000 -1150 °C	weiß / white	-	0	5	0	1	-	20	19	-	81	-	-	33
208	Drehen / Throwing	1000 -1280 °C	weiß-hellcreme / white-light cream	-	0	6	2	4	7	10	7	1	-	-	76	208
209	Drehen / Throwing	1000 -1300 °C	weiß-hell / white light	-	0	6	2	5	8	13	6	2	-	-	64	209
240	Drehen / Throwing	1000 -1240 °C	weiß-hellcreme / white-light cream	-	0	7	3	5	7	10	6	0,2	-	-	70	240
241	Drehen / Throwing	1000 -1280 °C	weiß-hellcreme / white-light cream	-	0	7	3	6	8	10	6	0,4	-	-	66	241
245	Drehen / Throwing	1000 -1150 °C	weiß-beige / white-beige	-	0	6	6	8	-	4	0,2	-	76	-	-	245
311	Drehen / Throwing	1000 -1140 °C	rot / red	-	0	8	6	8	-	7	2	-	77	-	-	311
1100	Drehen / Throwing	1000 -1280 °C	weiß-hell / white-light	-	0	5	-	-	9	-	-	0,1	-	-	56	1100
KACHEL- UND SKULPTURMASSEN / BODIES FOR STOVETILES																
441	Aufbauen / Modelling	1000 -1180 °C	weiß-hellcreme / white-light cream	0,2 - 0,8	45	4	1	2	-	12	9	-	71	-	-	441
468	Aufbauen / Modelling	1000 -1260 °C	weiß-hellcreme / white-light cream	0 - 0,5	40	5	2	4	5	9	6	2	-	-	62	468
474	Aufbauen / Modelling	1000 -1260 °C	weiß-hellcreme / white-light cream	0 - 1	40	5	2	4	5	9	6	3	-	-	64	254
478	Aufbauen / Modelling	1000 -1260 °C	weiß-hellcreme / white-light cream	0 - 2	25	6	3	4	6	8	5	1	-	-	64	478
480	Aufbauen / Modelling	1000 -1260 °C	weiß-hellcreme / white-light cream	0 - 2	40	4	2	3	4	10	7	4	-	-	63	480
552	Aufbauen / Modelling	1000 -1220 °C	rot / red	0 - 0,5	40	6	4	5	6	7	5	3	-	73	-	552
554	Aufbauen / Modelling	1000 -1220 °C	rot / red	0 - 1	40	6	4	5	6	8	5	3	-	73	-	554
559	Aufbauen / Modelling	1000 -1220 °C	rot / red	0 - 2	40	6	4	5	5	8	5	4	-	75	-	559
579	Aufbauen / Modelling	1000 -1120 °C	braun-schwarz / brown-black	0 - 2	40	6	4	5	-	7	6	-	74	-	-	579
584	Aufbauen / Modelling	1000 -1240 °C	lachs / salmon	0 - 1	40	5	3	4	6	9	5	2	-	-	61	584
592	Aufbauen / Modelling	1000 -1300 °C	flieder-gelb / lilac-yellow	0 - 0,5	40	7	4	6	8	13	6	3	-	-	71	592
596	Aufbauen / Modelling	1000 -1300 °C	flieder-gelb / lilac-yellow	0 - 1,5	40	6	4	6	7	14	7	5	-	-	70	369
1112	Aufbauen / Modelling	1000 -1280 °C	weiß-hell / white-light	0 - 1	20	5	-	-	7	-	-	2	-	-	52	1112
PORZELLANMASSEN / PORCELAIN BODIES																
1101 (Audrey Blackmann)	Aufbauen & Drehen / Modelling & Throwing	1200 -1280 °C	Porzellan weiß-transluzent / white-translucent	-	0	6	-	-	12	-	-	0,1	-	-	67	1101 (Audrey Blackmann)
1103 (White Passion)	Aufbauen & Drehen / Modelling & Throwing	1220 -1240 °C	Porzellan weiß-transluzent / white-translucent	-	0	4	-	-	10	-	-	0,1	-	-	69	1103 (White Passion)
1105 (Gießmasse)	Aufbauen & Drehen / Modelling & Throwing	1200 -1280 °C	Porzellanmasse / porcelain body	-	0	3	-	-	11	-	-	0,1	-	-	73	1105 (Gießmasse)

Produkt-Nr. Product No.	Anwendungen / Applications	Brennbereich / Firing range	Brennfarbe / Firing colour	Schamottierung / Chamotte		TS / DS %	Brennschwindung / Firing shrinkage (%)			Wasseraufnahme / Water absorption (%)			WAK x 10 ⁻⁷ °C ⁻¹ (20-500 °C) / CTE x 10 ⁻⁷ °C ⁻¹ (20-500 °C)			Produkt-Nr. / Product No.
				Körnung / grain size (mm)	Anteil / Portion (%)		1070°C	1140°C	1200°C 1240°C	1070°C	1140°C	1200°C 1240°C	1070°C	1140°C	1200°C 1240°C	
DREH- UND AUFBAUMASSEN / BODIES FOR THROWING AND HAND-BUILDING																
86	Aufbauen / Modelling	1000 -1140 °C	weiß-hellcreme / white-light cream	-	30	5	1	1	-	9	9	-	72	-	-	86
234	Aufbauen & Drehen / Modelling & Throwing	1000 -1240 °C	Paperclay weiß-hellcreme / white-light cream	-	0	7	5	7	8	11	6	3	-	-	62	234
254	Aufbauen & Drehen / Modelling & Throwing	1000 -1280 °C	weiß-hellcreme / white-light cream	0 - 0,2	25	7	5	6	7	9	6	1	-	-	64	254
264	Aufbauen & Drehen / Modelling & Throwing	1000 -1280 °C	weiß-hellcreme / white-light cream	0 - 0,5	25	6	3	6	6	8	4	1	-	-	64	264
267	Aufbauen & Drehen / Modelling & Throwing	1000 -1150 °C	weiß-beige / white-beige	0 - 0,2	15	6	4	6	-	4	2	-	70	-	-	267
284	Aufbauen / Modelling	1000 -1280 °C	weiß-hellcreme / white-light cream	0 - 1	25	6	3	5	6	8	4	1	-	-	64	284
354	Aufbauen & Drehen / Modelling & Throwing	980 -1200 °C	rot / red	0 - 0,2	25	7	5	6	7	6	3	1	-	72	-	354
356	Aufbauen / Modelling	1000 -1120 °C	braun-schwarz / brown-black	0 - 0,2	25	7	5	7	-	4	1	-	74	-	-	356
359	Aufbauen / Modelling	1000 -1220 °C	lachs / salmon	0 - 0,2	25	6	3	6	6	9	5	2	-	73	-	359
364	Aufbauen / Modelling	980 -1200 °C	rot / red	0 - 0,5	25	7	5	6	6	6	3	1	-	72	-	364
366	Aufbauen / Modelling	1000 -1120 °C	braun-schwarz / brown-black	0 - 0,5	25	7	5	7	-	4	2	-	74	-	-	366
369	Aufbauen / Modelling	1000 -1220 °C	lachs / salmon	0 - 0,5	25	6	3	4	6	9	6	2	-	72	-	369
371	Aufbauen & Drehen / Modelling & Throwing	1000 -1240 °C	grau-schwarz / grey-black	0 - 0,2	25	7	3	5	8	9	5	0,1	-	-	65	371
373	Aufbauen / Modelling	1000 -1240 °C	grau-schwarz / grey-black	0 - 0,5	30	6	3	4	6	9	5	1	-	-	66	373
376	Aufbauen / Modelling	1000 -1240 °C	grau-schwarz / grey-black	0,2 - 0,8	30	6	5	7	7	11	7	5	-	-	57	376
384	Aufbauen / Modelling	980 -1200 °C	rot / red	0 - 1	25	6	4	6	6	7	4	3	-	73	-	384
391	Modelling & Throwing	1000-1240°C	leather-cork	0 - 0,2	20	7		5	6-7		6	1-3			62	391
395	Aufbauen / Modelling	1000 -1200 °C	gelb / yellow	0 - 0,5	25	7	3	5	-	12	8	-	-	57	-	395
551	Modelling	1000-1240°C	red-redbrown	0 - 0,2	40	7		6	7		2	0,7			67	551
591	Aufbauen & Drehen / Modelling & Throwing	1000 -1280 °C	flieder-gelb / lilac-yellow	0 - 0,2	25	7	4	6	10	12	6	1	-	-	76	591
930 / 931	Aufbauen & Drehen / Modelling & Throwing	1000 -1280 °C	Spotmasse weiß-hellcreme / white cream	0 - 0,2	25	6	3	5	7	9	5	1	-	-	64	930 / 931
933	Aufbauen & Drehen / Modelling & Throwing	1000 -1240 °C	Spotmasse leder / leather	0 - 0,2	20	8	4	6	7	9	5	0,5	-	-	61	933
967-5	Aufbauen & Drehen / Modelling & Throwing	1100 - 1170 °C	Flammfest gelb / yellow	0 - 0,2	48	5	2	3	-	12	10	-	-	29	-	967-5
8251	Aufbauen / Modelling	1000 -1200 °C	Spotmasse leder / leather	0 - 0,5	15	8	4	6	7	8	5	1	-	-	66	8251
GIESSMASSEN / CASTING BODIES																
0033	Gießen / Casting	1000 -1150 °C	weiß / white	-	0	2	0	1	-	21	20	-	81	-	-	0033
0208	Gießen / Casting	1000 -1280 °C	weiß-hellcreme / white-light cream	-	0	4	2	4	7	10	7	1	-	-	76	0208
0209	Gießen / Casting	1000 -1300 °C	weiß-hell / white-light	-	0	3	2	4	6	13	8	1	-	-	64	0209
0245	Gießen / Casting	1000 -1150 °C	weiß-beige / white-beige	-	0	3	5	7	-	3	0,2	-	76	-	-	0245
1100	Gießen / Casting	1000 -1280 °C	weiß-hell / white-light	-	0	5	-	-	9	-	-	0,1	-	-	56	267